SPECIFICATION SHEET FOR CO SENSOR TYPE CO/MF-1000

PERFORMANCE CHARACTERISTICS

Neminal Dance	0 1000 mmm	
Nominal Range	0 – 1000 ppm	
Maximum Overload	2800 ppm	
Expected Operation Life	2 years in air	
Output Signal	50 ± 15 nA/ppm	
Inboard Filter	To remove H2S and SO2	
Resolution	2 ppm	
Temperature Range	- 20 ℃ to + 50 ℃	
Pressure Range	Atmospheric ± 10 %	
Pressure Coefficient	No data	
t90 Response Time	< 25 sec	
Relative Humidity Range	15 % to 90 % R.H.	
	non-condensing	
Typical Baseline Range (pure air, 20℃)	- 4 ppm to +6 ppm	
Maximum Zero Shift (+20℃ to +40 ℃)	18 ppm equivalent	
Expected Long Term Output	< 2 % signal	
Drift	loss/month	
Recommended Load Resistor	10 Ohm	
Bias Voltage	Not required	
Repeatability	< 2 % of signal	
Output Linearity	Linear	

CROSS-SENSITIVITY DATA

Interfering Gas	Concentration	Reading
H ₂	100 ppm	< 40 ppm
H ₂ S	10 ppm	~ 0 ppm

Performance data conditions: 20 °C, 50% RH and 1013 mbar


APPLICATIONS


Safety and Environmental Control For Portable Gas Detectors

PHYSICAL CHARACTERISTICS

Weight	~ 5.4 g
Position Sensitivity	None
Storage Life	Six months in
_	container
Recommended Storage	5 °C – 20 °C
Temperature	
Warranty Period	12 months from date
-	of dispatch

Miniature-Size Outline Dimensions





REV.: 2/2008


Phone: +41 43 311 72 00 Fax : +41 43 311 72 01 Email: info@membrapor.ch www.membrapor.ch Page 1 of 1

MEMBRAPOR AG Birkenweg 2 CH-8304 Wallisellen Switzerland

SPECIFICATION SHEET FOR CO SENSOR TYPE CO/MF-1000

TEMPERATURE DEPENDENCE

The output of an electrochemical sensor varies with temperature. The graphs below show the variation in output with temperature for this type of sensor. The results are shown in the graphs as a mean for a batch of sensors, along with confidence intervals corresponding to ± 3 times the standard deviation. The sensitivity dependence is expressed as a percentage of the signal at 20 °C.



The data contained in this document is for guidance only. Membrapor AG accepts no liability for any consequential losses, injury or damage resulting from the use of this document or the information contained within it. The data is given for guidance only. Customers should test under their own conditions, to ensure that the sensors are suitable for their own requirements.

REV.: 2/2008

Phone: +41 43 311 72 00 Fax : +41 43 311 72 01 Email: info@membrapor.ch www.membrapor.ch Page 2 of 2

MEMBRAPOR AG Birkenweg 2 CH-8304 Wallisellen Switzerland